


DATA SHEET	44423228
EPIC[®] MHS Bus 2x(4) CM	Valid from: 22.02.2017

Description

- Shielded modul for data and signal transmission
- Crimp connection for permanent vibration-proof contact
- EPIC[®] MH system is mateable with the market standard
- The mix of different functions is one plug guarantees high flexibility



General characteristics

Contact type	plug
Number of contacts	8
Mating cycles	500
Material	PA
Inflammability class acc. with UL 94	V0
Pollution degree	3
Temperature range	-40° C to +125° C
Termination methods	crimp termination: 0.14 – 2.50 mm ² Epic [®] MH 6 multi-frame Epic [®] MH 10 multi-frame Epic [®] MH 16 multi-frame Epic [®] MH 24 multi-frame
Suitable frame	Epic [®] H-BE 1.6 machined contacts Epic [®] MH Bus PIN 1x(4) contact holder
Suitable contacts	

Electrical characteristics

Rated voltage	50 V
Rated impuls voltage	0.8 kV
Rated current	10 A





Standards/Approvals

Fire protection on railway vehicles	according EN 45545-2 requirement sets R22 and R23 hazard level HL1, HL2 and HL3
-------------------------------------	---



DATA SHEET	44423228
EPIC® MHS Bus 2x(4) CM	Valid from: 22.02.2017

Drawings



Note

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP Released: IVSE1/PDP	Document: DB44423228EN Version: 00	Page 2 of 2
---	---------------------------------------	---------------------------

We reserve all rights according to DIN ISO 16016.