



12W

VT-814 12W LED WALL LIGHT COLORCODE:3000K -BLACK BODY

Lumens 1320	Beam Angle 350	Dimensions 230x54x97mm
-----------------------	--------------------------	----------------------------------

Warm White
SKU:8293

2 YEARS
WARRANTY

SENSOR
COMPATIBLE




Technical Information

Instant Start:	0-100% in 11s	IP Rating:	IP65
Watts:	12	Dimmable:	No
Lumens:	1320	Warranty (Years):	2
Beam Angle:	350	PF:	>0.5
Unit Color:	Black	CRI:	>80
Body Type:	Aluminium	Operation Temperature:	-20 to +45°C
Long life:	20,000 Hours	Input Power:	AC:110-240V,50/60Hz
LED Chip Type:	SMD	Sensor Compatibility:	Yes

Features

- ✓ Designed for perfection - 360 Rotatable wall light
- ✓ High quality LED chips for a reliable lighting effect
- ✓ Available in different unit_colors and color temperature options - Warm White and Day White
- ✓ Excellent heat dissipation
- ✓ Easy installation and Maintenance
- ✓ Applications - Perfectly suitable for Indoor and Outdoor applications

Note:  Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	1.03
Unit CBM	0.00042

Listing Details

EAN Code	3800157629874
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	600

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES