



OD9238 IP68 Series



DC Fans - 24, 48V
92mm x 38mm (3.62" x 1.5")



Frame	PBT, UL94 V-0 Plastic	Operating Temperature -20°C ~ +65°C Storage Temperature -20°C ~ +75°C Life Expectancy 60,000 Hours (L10 at 45°C) Available Options Tachometer Output Alarm Output PWM Speed Control Thermistor Speed Control Other IP Ratings Other Voltages Weight: 0.44 lbs
Impeller	PBT, UL94 V-0 Plastic	
Connection	2x Lead Wires, 24 AWG	
Motor	Brushless DC, Auto Cutoff, Auto Restart, Polarity Protected, Electronically Protected, IP68	
Bearing System	Ball Bearings	
Dielectric Strength	500VDC/min, <5mA	
Insulation Resistance	≥10MΩ @ 500V DC	



Part Number	Rated Voltage (Volts DC)	Voltage Range (Volts DC)	Input Power (Watts)	Rated Current (Amps)	Rated Speed (RPM)	Max Airflow (CFM)	Noise Level (dBA)	Max Static Pressure ("H ₂ O)
OD9238-24HHBIP68	24 VDC	15 ~ 26	10.8	0.45	5000	110	58.3	0.86
OD9238-24HBIP68	24 VDC	15 ~ 26	9.6	0.40	4500	100	56.1	0.70
OD9238-24MBIP68	24 VDC	15 ~ 26	7.2	0.30	4000	89	53.7	0.55
OD9238-24LBIP68	24 VDC	15 ~ 26	4.8	0.20	3500	78	50.2	0.42
OD9238-48HHBIP68	48 VDC	28 ~ 52	14.4	0.30	5000	110	58.3	0.86
OD9238-48HBIP68	48 VDC	28 ~ 52	12	0.25	4500	100	56.1	0.70
OD9238-48MBIP68	48 VDC	28 ~ 52	9.6	0.20	4000	89	53.7	0.55
OD9238-48LBIP68	48 VDC	28 ~ 52	7.2	0.15	3500	78	50.2	0.42