

Adjustable clamps

Depressed centre



Version:

- Heat-treated steel
- Painted
- Single depressed centre



Art. no.	26138 040
Slot width	14 mm
Length	125 mm
Suitable cheese-head screw DIN 912	M12, M14
Slot length	40 mm
Clamping shoe height	20 mm
Clamping shoe width	40 mm
Height	18 mm
Width 3	20 mm
Height 2	16 mm
DIN	6316

EAN-Code

4020772071059