

## Torque screwdrivers

TORSIOMAX 775, with calibration certificate



### Application:

For torque-controlled screw tightening in the CNm range.

### Execution:

- 1/4-inch internal hexagon (F 6.3 DIN 3126)
- Releases itself
- For individual and series tightening
- With unlatch coupling, anti-clockwise/clockwise tightening
- Comes with certificate



|                                 |                  |
|---------------------------------|------------------|
| <b>Art. no.</b>                 | <b>52208 010</b> |
| <b>Brand</b>                    | STAHLWILLE       |
| <b>Manufacturer Part Number</b> | 51060003         |
| <b>Min./max. torque</b>         | 2.0-30 Ncm       |
| <b>Scale value</b>              | 0.2              |
| <b>Blade diameter</b>           | 1/4 in           |
| <b>Handle length</b>            | 105 mm           |
| <b>Material of handle</b>       | Aluminium        |
| <b>Error limit (%)</b>          | 6 %              |
| <b>Calibration certificate</b>  | Yes              |
| <b>Gross Weight</b>             | 0.242 kg         |
| <b>Product Group</b>            | 531              |

### EAN

4018754141623