

## Pneumatic ratchet screwdriver 9022P-XLG

Square drive 1/2 inch – extra long and slim design



### Application:

For manual tightening with torques up to 400 Nm

### Execution:

- Extra long and slim design
- Clockwise/anti-clockwise rotation: single-stage
- Cold-insulating handle

### Advantage:

- Extra long and slim design
- low-vibration
- Also reaches into extremely obstructed spaces and tolerates high manual tightening forces

### Delivery:

includes coupling plug



<b>Art. no.</b>	<b>75053 425</b>
<b>Brand</b>	HAZET
<b>Manufacturer Part Number</b>	9022P-XLG
<b>Model</b>	9022P-XLG
<b>Max. tightening torque</b>	94 Nm
<b>Max. idle speed</b>	160 rpm
<b>Air consumption</b>	99 l/min
<b>Tool holding device</b>	1/2-inch external square
<b>Length</b>	550.4 mm
<b>Connection thread</b>	G 1/4 inch
<b>Inner hose diameter</b>	10 mm
<b>Operating pressure</b>	6.3 bar
<b>Sound-pressure level</b>	93.7
<b>Weight</b>	2.1 kg
<b>With right/left-hand rotation</b>	Yes
<b>Gross Weight</b>	2.370 kg
<b>Product Group</b>	738

### EAN

4000896222513