



Model / Order-No.	TT-HVP 15B / 15010
Division Ratio	1000:1
Input Resistance	100MΩ
Input Capacitor	3,0pF ± 0,5pF
Max. DC+AC peak	20kV CAT 0
Max. AC RMS.	7kV CAT 0
Max. DC	10kV CAT 0
Band Width	DC~40MHz (-3dB)
Rise Time	8,75ns
Signal / Noise	DC: > 60dB @ 1kHz ; > 50dB @ 1MHz
DCV Accuracy	≤ 6%
Temp. Coefficient	≤ 200 ppm/°C
Compensation Range	5pF ~ 50pF
Safety Standard	meets EN61010-031:2015
Measurement Category	CAT 0 / Pollution Degree 2
Cable Length	2m ± 0.2m
Operation Temp.	-10°C to 55°C
Humidity	85% RH or less (@ 35°C)
Storage Temp.	-20°C to 70°C
Color: Handel / Body	Black / Yellow
Weight / Volume	250g / 75(W) x 75(H) x 340(L) mm