



Pos	Dim. A	Dim. B	Dim. C	Dim. D	Dim. E	Dim. F	Pos	Dim. A	Dim. B	Dim. C	Dim. D	Dim. E	Dim. F
8	14.86	8.89	7.62	14.66	13.55	5.00	30	42.80	36.83	35.56	42.80	13.45	4.85
10	17.40	11.43	10.16	17.20	13.55	5.00	34	47.88	41.91	40.64	47.68	13.55	5.00
12	19.94	13.97	12.70	19.74	13.55	5.00	36	50.42	44.45	43.18	50.22	13.55	5.00
14	22.48	16.51	15.24	22.28	13.55	5.00	40	55.50	49.53	48.26	55.30	13.55	5.00
16	25.02	19.05	17.78	24.82	13.55	5.00	44	60.58	54.61	53.34	60.38	13.55	5.00
18	27.56	21.59	20.32	27.36	13.55	5.00	50	68.20	62.23	60.96	68.40	13.45	4.85
20	30.10	24.13	22.86	29.90	13.55	5.00	60	80.90	74.93	73.66	80.70	13.55	5.00
24	35.18	29.21	27.94	34.98	13.55	5.00	64	85.98	80.01	78.74	85.78	13.55	5.00
26	37.72	31.75	30.48	37.52	13.55	5.00							

ORDER INFORMATION

C3001 — **xx** **Y** **Y** **S** **B** **0** **0** **R**

1 2 3 4 5 6 7 8

- 1. CONTACT No. : 08~64
- 2. FUNCTION : Y : WITH S/R
N : WITHOUT S/R
- 3. BODY OPTION : Y : WITH BUMP
N : WITHOUT BUMP
- 4. CONTACT PLATING : T : TIN
S : SELECTIVE GOLD
G : GOLD FLASH
- 5. INSULATOR COLOR : B : BLACK
- 6. FILL IT WITH "0"
- 7. FILL IT WITH "0"
- 8. ROHS

RoHS Compliant	HSM 玄茂科技股份有限公司 HSUAN MAO TECHNOLOGY CO., LTD.	
APPD. 核准 Betty		TOLERANCE 容許公差 .0 ±0.2 .00 ±0.05 ANG. ±
DWG. 製圖 Betty		PART NAME 品名 2.54mm X 2.54mm IDC SOCKET XXP WITH S/R WITH BUMP SELECTIVE GOLD BLACK
DATE 制表日 2007/06/12	UNIT 單位 M M	INSULATOR
PAGE 張數 1 OF 1	REV. 版次 A	PART NO. 料號 C3001-XXYYSB00R