

FEATURES

- Heavy duty steel construction
- Both ratchet and free run operating
- Spring protector
- Temperature range - 5°C to +60°C
- Supplied with wall and ceiling bracket

RS PRO Air Hose Blue Polyurethane 12mm x 15m HR Series Series

RS Stock No.: 788-3736



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Brought to you by RS Pro, a range of professional polyurethane braid air hoses, suitable for various applications. The highlight of these hoses would be the handy automatic hose reel, which would be a god send in environments where a particular length is needed, or situations where hoses won't have to be gathered up after use. All models are highly reliable and excellent quality.

General Specifications

Colour	Blue
Material	Polyurethane
Number Of Tubes	2
Special Features	1/4" BSPT Female Swivel Unions
Application	Pneumatic Equipment, Tools & Compressors

Mechanical Specifications

Hose Inside Diameter	8mm
Hose Outside Diameter	12mm
Length	1m (Inlet), 15m (Outlet)

Operation Environment Specifications

Maximum Operating Pressure	15bar
Minimum Operating Temperature	-5°C
Maximum Operating Temperature	60°C
Burst Pressure	60bar

Article No	Hose ID	Hose Length (inlet)	Hose Length (outlet)	W.P	B.P	Thread Size (inlet+outlet)	Weight (N.W.)
788-3739	8mm	1M	10M	15bar	60bar	1/4"+1/4"	9kgs
788-3732	8mm	2M	10M	15bar	60bar	3/8"+3/8"	9kgs
788-3736	8mm	1M	15M	15bar	60bar	1/4"+1/4"	9kgs