SPECIFICATION

ITEM NO.	APPA50BK
SPECIFICATION	0.32/1×2×1M Teflon K-type ±5%
PERFORMANCE	BEAD PROBE With teflon wire & mini connector. For electronic parts Temp. Temp. : -40 to 204℃ Response time : 4 to 7 Sec Accuracy ±0.3%
MATERIAL	Probe : Covered with teflon wire Temp. : -40℃ to 204℃ Handle : ABS 、 Fireproof Temp. : -50℃ to 200℃
THERMOCOUPLE WIRE TEMP.	-40℃ to 204℃
CHEMICAL RESISTANCE	Not for liquid 、 water 、 acid and base