

KVT

Split cable glands




1

Type	Order No.	Grommets small large	Thread Thread length	PU	Description
------	-----------	------------------------	----------------------	----	-------------

KVT 50 2	<input type="checkbox"/> 45204 <input type="checkbox"/> 45030	2 -	M50 × 1.5 Length: 14 mm	5	
KVT 50 2 + KGM-SUB-D25	<input type="checkbox"/> 45206 <input type="checkbox"/> 45031	2 -	M50 × 1.5 Length: 14 mm	5	
KVT 63 1	<input type="checkbox"/> 45212 <input type="checkbox"/> 45112	- 1	M63 × 1.5 Length: 14 mm	5	
KVT 63 4	<input type="checkbox"/> 45215 <input type="checkbox"/> 45115	4 -	M63 × 1.5 Length: 14 mm	5	

Advantages

- Insertion of pre-terminated cables
- Warranty on pre-terminated cables remains
- Retrofitting and maintenance can be carried out easily and quickly
- High packing density, wide variety of grommets
- Suitable for standard or metric cut-outs
- Polyamide locknuts are included in the shipment



Specifications

Material	Polycarbonate (PC)
Colour	<input type="checkbox"/> grey (similar RAL 7035) <input type="checkbox"/> black
Flame class	UL94-V0, self-extinguishing
Protection class	IP54, with gasket and correct selection of the cable grommets (certified according to DIN EN 60529:2000-09)
Temperature	- 30°C to + 100°C (static)
Properties	Halogen free, silicone free
Cut-out dimension	Metric standard sizes

Accessories

KT Cable grommets	38 - 42
KVT-EMC Brackets	121
Locknuts	158

* Only valid for grey product types