## **Product Specification PDF**



Date	Correct as of 15th May 2019
Brand	C.K
Product	T3885
Description	Ecotronic ESD Side Cutters (Slim)
Barcode	5013969938852
Commodity code	8203200000
Country of origin	TW



Features & Benefits Lightweight, precision side cutters for fine cutting applications Suitable for cutting soft copper wires of up to

1.3mmØ / 16AWG Slim, tapered head for access in confined spaces Sharp, precision ground cutting edges with a full flush cut Special tool steel blade, hardened for long-term cutting performance Elecro-static discharging handles ~ dissipative 10? Contoured, dual component handle design for comfortable working Black oxidised finish for corrosion resistance and reduced glare Smooth-action return spring for convenience during repetitive work Joint with durable stainlesss steel rivet Technical information: Total length: 139 mm Blade length: 9 mm Cutting angle: 21° Head Height (from joint to tip): 18 mm Head Width (Widest point): 10 mm Steel Thickness: 2,5 mm

Cutting Capacity (Copper only) : 1,3 mm / 16 AWG

Applicable Standards IEC 61340 5.1 & 5.2 Health & Safety None applicable

Warranty C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through

normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures					
	Product only	Product & primary packaging	Secondary packaging	Transit packaging	
Item Quantity	1	1	6	120	
Width mm	139	220	21.6	470	
Depth mm	70	80	8.4	470	
Height mm	20	2.5	10.8	240	
Weight	76	91	615	13.3	
Packaging Information	Card use	0	Box	Case	
	Card gms	0	69	1012.5	
	Plastic use	Blister	0	-	
	Plastic gms	15	0	-	
	Metal use	0	0	-	
	Metal gms	0	0	0	
	Timber use	0	0	-	
	Timber gms	0	0	0	