


LUGS 32 FOR SIGNAL TRANSFER


250V / 8 A

32-pole
Screw plug-in terminals

[Link to Product](#)

Illustration





Product may differ from Image

Technical Data

Operating voltage	max. 250 V AC
Operating current per bit	max. 10 A
Material group	(EN 60664-1) over voltage, category I

General data

Mounting method	DIN-rail mountable (EN 60715)
Connection	Screw plug-in terminal: max. 4 mm ² , single wire
Temperature range	-20...+60 °C
Dimensions H × W × D	75×90×66 mm

Commercial data

country of origin	CZ
customs tariff number	85369010
minimum order quantity	1