









Order-No.	Shell Size / for No. of Contacts	A	B	C	D	E	∅F	G	H	J	K	L	M	N	P	Q
FKC1A	1 / 9	10	25	31.8	39.3	15.8	3.5 - 8.6	20	41.6	11.6	17	19	19.3	20.2	12	3.9
FKC2A	2 / 15	16	33.3	41.2	45	16.2	3.5 - 8.6	28.4	47.8	11.6	24.8	26.9	27.9	25.7	12	3.9
FKC3A	3 / 25	28	47	54.9	52	16.2	4 - 12	42.1	54.8	11.6	38.2	40.5	41.4	25.3	18	3.9
FKC4A	4 / 37	44.4	63.5	71.4	55	18.9	6 - 13	58.6	57.8	12.1	55	57.2	58.1	22.5	21	3.9
FKC5A	5 / 50	42	61.1	69	55	19.5	6 - 14	56.2	57.8	15	52.6	54.7	55.7	22.5	21	4.1



No.	St.	Part	Type Description / Material
9	1	Contact spring	Spring steel
8	2	Locking screw	FVSI/5-K1163 4-40 / Steel
7	0/1	Cable reduction plate	nickel plated
6	1	Strain relief	nickel plated
5	2	Cable clamp screw	nickel plated
4	1	Cable clamp	zinc plated
3	1/2	Shell screw	tin plated
2	2	Catch spring	zinc plated
1	1	Hood	PEI
			FKC1-5A / ABS / PC+ABS
			Surface plating/Colour/Class

COMMENT: ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT, IT MAY NEITHER BE DUPLICATED NOR MADE AVAILABLE TO A THIRD PARTY. AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.

RoHS compliant

① max. torque are 40 Ncm  
Hood is snapped together  
Part-No. 3, 4, 5, 6 and 9 not mounted  
FKC3-5A without Part-No. 7  
FKC1-3A with 1 Shell screw (Part-No. 3)  
FKC4-5A with 2 Shell screws (Part-No. 3)

②

Cable reduction plate (Part-No. 7) only in sizes 1 and 2

4-40UNC-2A

reverse side 1:1

FKC3A  
FGTgroup.com

SCALE 2:1

Plastic Hood

FKC1-5A

ORIGINAL: DIN A3-DRAWING AS A FILE

REPLACEMENT FOR: FKC1-2AG,FKC3AG,FKC4AG,FKC5AG,ACAD

DATE 02-07-2008

DATE 08-05-2008

CH-NO.

DATE

CH-NO.

DATE

CH-NO.

DATE

REV. 2

REV. 1

REV. 2

REV. 1

REV. 2

REV. 1

REV. 2

REV. 1

REV. 2

REV. 1