

Item no.: 224-104
 Product description: LIGHTING CONNECTOR VERSION FOR INCREASED CONTINUOUS SERVICE TEMPERATURE OF 120°C



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

Product group	7 (Push Wire Conn.)
Cross section [mm ²]	1 - 2.5 mm ²
Cross section [AWG]	14 - 12 AWG
Wiring method	e
Connection method	CAGE CLAMP® CONNECTION
Cross section [mm ²]	0.5 - 2.5 mm ²
Cross section [AWG]	20 - 16 AWG
Wiring method	e+f
Measured voltage EN	400 V
Measured shock voltage	4 kV
Pollution degree	2
Current intensity EN	24 A
Weight	2.34 g
Color	black
Wiring type	Side-entry
No. of connection Points	2
No. of potentials	1
Height	15.5 mm
Height	0.61 in
Width	8.5 mm

Width
Depth

0.335 in
20.5 mm



Depth	0.807 in
Strip length from	9 mm
Strip length to	11 mm
Strip length	0.39 in



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
224-104	ABS	04-HG476172/1-PDA	400	24	1-2,5/0,5-2,5
224-104	BV	11914/BO	300	24	2,5
224-104	CCA	DK2527	400	24	2,5
224-104	CSA	154112-1059435	300		14-12
224-104	DEMKO	143835-01	400	24	2,5
224-104	DNV	E-9215	400	24	2,5
224-104	FIMKO	163400-01			2,5
224-104	GL	17294-00HH	300	24	2,5
224-104	KEMA	96.1739.01	400	24	2,5
224-104	LR	04/20013(E3)	400	24	2,5
224-104	NEMKO	P96191377			2,5
224-104	ÖVE	1193-032-02	400	24	1-2,5/0,5-2,5
224-104	PSE	JET0695-43040-1001	300	20	14-12
224-104	RMR	11130002	400	24	1-2,5/0,5-2,5
224-104	SEMKO	9617079			2,5
224-104	UL	E69654	300	20	14-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected