

Series 600 zinc-plated table trolley, load capacity 500 kg

Load areas 1000x700 mm and 1200x800 mm



Application:

For safely and easily transporting goods, parts and materials.

Execution:

- Load areas covered with 2 mm electrolytically zinc-plated sheet steel
- Height of the lower load area 260 mm
- Distance between the load areas 580 mm
- Frame made of 25 mm steel tubing, galvanised
- 2 fixed castors and 2 swivel castors made of solid rubber 200 x 50 mm
- Load capacity of load areas: 250 kg each
- The 600 series also includes cabinet trolleys, front wall carriages and other variants

Advantage:

- No need to go far to find your tools - work equipment is provided directly at the workstation
- Galvanised load areas - durable and robust



Art. no.	50260 043
Brand	KONGAMEK
Manufacturer Part Number	KM637-2
Load-carrying capacity	500 kg
Length	1100 mm
Length x width x height	1100 x 700 x 870 mm
ESD-capable	No
Number of loading surfaces	2
Loading surface size	1000 x 700 mm
Loading surface length	1000 mm
Loading-surface width	700 mm
Height	870 mm
Number of fixed rollers	2
Number of steering rollers	2
With wheel lock	No
Wheel width	50 mm
Wheel diameter	200 mm
Material of wheel	Solid rubber
Colour	Silver coloured
Surface	Zinc plated
Gross Weight	57.500 kg
Product Group	5AT

EAN

7350050352486