

Kaliflex flex cold-light lamp

Base height 111 mm, lamp head length 288 mm

Execution:

- Powerful luminosity and large light field
- Flexible gooseneck tube made of metal, with rubber coating
- Ballast unit integrated in the base of the lamp
- Switch integrated in the lamp head
- Lamp head and housing made from impact-resistant, non-flammable plastic
- Connection line 1.6 m H03RN-F, 230 V
- Base height 111 mm, lamp-head length 288 mm
- Compact 11-W fluorescent tubes/G23 base

Delivery:

With connection cable, magnet, screw clamps, screws

Art. no.	56879 120
Power rating	11 W
Arm length	700 mm
IP protection class	IP 40
Gross Weight	2.572 kg
Product Group	5ID

