


Spade terminals, PVC insulated



SPECIFICATION:

Material	Copper
Surface material	Tin-plated
Max. temperature	+105 °C



PRODUCT RANGE:

Article Nr.	Cross-section	AWG	Stud Size	Colour	A	B	L	t
RND 465-00659	0.5...1.5 mm ²	22-16 AWG	#4	Red	5.7 mm	3.2 mm	23 mm	0.75 mm
RND 465-00660	0.5...1.5 mm ²	22-16 AWG	#8	Red	6.4 mm	4.3 mm	23 mm	0.75 mm
RND 465-00661	0.5...1.5 mm ²	22-16 AWG	#10	Red	8 mm	5.3 mm	23 mm	0.75 mm
RND 465-00662	1.5...2.5 mm ²	16-14 AWG	#8	Blue	6.4 mm	4.3 mm	23 mm	0.8 mm
RND 465-00663	1.5...2.5 mm ²	16-14 AWG	#10	Blue	8 mm	5.3 mm	23 mm	0.8 mm
RND 465-00664	4...6 mm ²	12-10 AWG	#10	Yellow	9 mm	5.3 mm	27.7 mm	1 mm
RND 465-00665	4...6 mm ²	12-10 AWG	1/4	Yellow	9 mm	6.4 mm	31.7 mm	1 mm