# Lighting

**PHILIPS** 



# **Trueforce Core LED SON-T**

# TForce Core LED road 40W 730 E40 MV

The new Philips Trueforce Core LED SON-T lamps offer you an easy, short-payback LED solution to replace High Intensity Discharge (HID) lamps. This new generation of products brings all the energy-efficiency and long-lifetime benefits of LED to HID replacement, while providing instant saving with a low initial investment. Furthermore, they're designed to have the same lamp size and light distribution as other HID lamps, so you will never know the difference. All thanks to our High-Power LED filament technology. Plus, its unique IP65 design means it can be used for outdoor applications.

### **Product data**

General information	
Cap-Base	E40 [ E40]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	15000X
Flux measurement reference	Sphere
Light technical	
Color Code	730 [ CCT of 3000K]
Luminous Flux (Nom)	7200 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 К
Luminous Efficacy (rated) (Nom)	180.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	40 W
Lamp Current (Nom)	178 mA
Wattage Equivalent	100 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	58 ℃
Controls and dimming	
Dimmable	No



## **Trueforce Core LED SON-T**

Mechanical and housing	
Bulb Finish	Clear
Bulb Shape	T-shape
Approval and application	
Energy Efficiency Class	С
Energy Consumption kWh/1000 h	40 kWh
EPREL Registration Number	574359
Product data	
Full product code	871951431633100

Order product name	TForce Core LED road 40W 730 E40 MV
EAN/UPC - Product	8719514316331
Order code	929002485202
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929002485202
Net Weight (Piece)	0.157 kg


#### Dimensional drawing



Product	D	С
TForce Core LED road 40W 730 E40 MV	46 mm	225 mm

TForce Core LED road 40W 730 E40 MV

#### Photometric data



LEDTForce Core road 40W Tshape E40-LDD


1 x TForce 48W 3000K \$21082485380	
	1 x 7380 be

ion Liefrcing B

LEDTForce Core road 40W Tshape E40 730-GUL


# **Trueforce Core LED SON-T**

Photometric data



LEDTForce Core road 40W Tshape E40 730-POC

### Lifetime



LEDspots LED 25K

LEDspots LMP 25K



© 2022 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2022, February 11 - data subject to change