

PneumoCord

Der pneumatische Spanner für sämtliche textile Bänder bis 32 mm

PneumoCord ermöglicht effektives und schnelles Sichern von Gütern mit Fadenbändern, Kompositbändern sowie gewebten Bändern und Schnallen. Bei Verwendung von Drahtschnallen kann durch die integrierte Schneideeinheit ohne vorheriges Ablängen des Bandes gearbeitet werden.

Die Version RV hat eine links- / rechts-drehende Spanneinheit. So sind größte Spannwege handhabbar, wenn das Band nicht um das Packgut von Hand vorgestraft werden kann. Auch kann der Schneide- und Auslösevorgang mit weniger Kraftaufwand erfolgen.

Optional verfügbar ist ein Aufhängebügel für das Arbeiten mit Federzug / Balancer. Der Handschutzbügel (für Version PRC) vermindert Verletzungsrisiken. Die Rundumreifer (für Version PRC RV) ermöglichen ein zuverlässiges Sichern von Packstücken mit keiner oder nur sehr geringer Auflagefläche.



- Einfachste Handhabung, geringes Gewicht
- Robuste Ausführung konzipiert für Dauereinsatz
- Hohes Spannvermögen von max. 7.500 N; Spannleistung durch Vorwahl des Betriebsdrucks gesteuert
- Integrierte Schneideeinheit
- Diverses optionales Zubehör verfügbar (Aufhängebügel, Handschutzbügel, Rundumreifer)

The pneumatic tensioner for all textile straps up to 32 mm width

PneumoCord allows effective and quick securing of goods with corded, composite and woven straps and buckles. The build-in cutter enables to work without crosscutting the strap when using wire buckles.

The version RV has a left / right turn tensioning unit. Thus greatest ways of tensioning are manageable if the strap can not be pre-tensioned around the good by hand. Also the cutting and release operation can be accomplished with less effort.

For working on a balancer there is optional available a hanger bow. The hand protection bow (for version PRC) minimizes the injury risks. The round bundlers (for version PRC RV) enable a reliable way of securing goods with none or only a very small contact face.

- Easiest handling, light weight
- Rugged construction designed for continuous use
- High tensioning capacity of max. 7,500 N; tensioning power is controlled by pre-selection of operating pressure
- Integrated cutting unit
- Optional accessories available (hanger bow, hand protection bow, round bundler)



Aufhängebügel / Handschutzbügel
Hanger bow / hand protection bow



Rundumreifer
Round bundler



PneumoCord
PRC



PneumoCord
PRC RV

Technische Daten – Specifications

Typ Model	PRC	PRC RV
Art. Nr. Stock No.	089171	089172
Bandsorte Strap type	Kraftband, Kompositband, gewebtes Band Hot melt strap, composite strap, woven strap	
Bandbreite / Dicke Strap width / Thickness	≤ 32 mm (1 1/4") / 2,0 mm	
Verschluss Lock	Reibverschluss mit Schnalle (Draht, Key-Lock, Doppelsteg) Friction lock with buckle (wire, key-lock, double bar)	
Druckluft Compressed air	max. 7,5 bar (100 psi) 610 l/min	
Länge / Breite / Höhe Length / Width / Height	29 x 12 x 20 cm	31 x 12 x 20 cm
Gewicht Weight	3,8 kg	4,0 kg

Zubehör – Accessories

Art. Nr. / Bezeichnung Stock No. / Description	038-060 Handschutzbügel 038-060 Hand protection bow	-
Art. Nr. / Bezeichnung Stock No. / Description	038-900 Aufhängebügel 038-900 Hanger bow	
Art. Nr. / Bezeichnung Stock No. / Description	-	036-290 Rundumreifer RBE 19 mm 036-290 Round bundler RBE 19 mm
Art. Nr. / Bezeichnung Stock No. / Description	-	036-390 Rundumreifer RBF 25 mm 036-390 Round bundler RBF 25 mm
Art. Nr. / Bezeichnung Stock No. / Description	-	037-490 Rundumreifer RBG 32 mm 037-490 Round bundler RBG 32 mm