



Tragfähigkeit in kg für Anschlagseile

Sicherheitsfaktor 5:1



Ausführung	1-Strang			2-Strang		4-Strang		
	Durchmesser mm	direkt	parallel	geschnürt	β 0-45°	β 45-60°	β 0-45°	β 45-60°
8		700	1.400	560	950	700	1.500	1.050
10		1.050	2.100	840	1.500	1.050	2.250	1.600
12		1.550	3.100	1.200	2.120	1.550	3.300	2.300
13		1.800	3.600	1.440	2.500	1.800	3.850	2.700
14		2.120	4.240	1.700	3.000	2.120	4.350	3.150
16		2.700	5.400	2.100	3.850	2.700	5.650	4.200
18		3.400	6.800	2.700	4.800	3.400	7.200	5.200
20		4.350	8.700	3.500	6.000	4.350	9.000	6.500
22		5.200	10.400	4.000	7.200	5.200	11.000	7.800
24		6.300	12.600	5.000	8.800	6.300	13.500	9.400
26		7.200	14.400	5.800	10.000	7.200	15.000	11.000
28		8.400	16.800	6.700	11.800	8.400	18.000	12.500