


Shape

KSSG3108



Model Number	KSSG3108
Rated Input (W)	0.1
Maximum Input (W)	0.2
Impedance (Ω)	$8 \pm 20\% @ 1\text{KHz} 1.0\text{V}$
Rated Frequency (Hz)	$1250 \pm 20\% @ 1.0\text{V}$
Sound Pressure Level (dB)	$92 \pm 3\text{dB} (0.1\text{W}/10\text{cm}), 85 \pm 3\text{dB} (1\text{W}/1\text{m}) @ 1.5\text{K}, 2.0\text{K}, 2.5\text{K}, 3.0\text{KHz}$
Frequency Range (Hz)	Fo--4K
Magnet (mm)	$\phi 16.0 \times 7 \times 2.5$ Ferrite
Operating Temperature ($^{\circ}\text{C}$)	-20 ~ +55
Weight (Gram)	10.0
Material	ABS UL-94 1/16" HB

Dimension



Tol : ± 0.5 Unit : mm

Characteristic

