






Frame type plug-in units PRO ServicePLUS

Individual components

Front panels, front handles

	Front panel	Shieldable front panel, U profile		Trapeziform handle, grey (without extraction function)		
	unshielded	Front panel	Textile EMC gasket	Grey	Black	
 <p style="font-size: 8px;">04808124</p>	 <p style="font-size: 8px;">04808060</p>	 <p style="font-size: 8px;">04808061</p>	 <p style="font-size: 8px;">04808062</p>	 <p style="font-size: 8px;">04808063</p>		
<p>Supplied quantity for assembly of 5 frame type plug-in units</p>	<p>Al, 2.5 mm, front anodised, rear iridescent green chromated, cut edges blank</p>	<p>Al extrusion, alignment pin pressed-in, front anodised, rear conductive</p>	<p>always fixed laterally on the front panel, in the groove of the profile, textile gasket, core: foam, sleeve: textile cladding with CuNi coating, UL 94 V-0, temperature range -40 ... 70 °C</p>	<p>handle: PPE, UL 94 V-1; identification plate: Al, 1.5 mm, anodised, cut edges plain; please order clip separately (included in mounting kit for five plug-in units or individual parts) 7.78</p>		
	1 piece (SPQ 5) ¹⁾	1 piece (SPQ 5) ¹⁾	PU 10 pieces	PU 100 pieces	1 piece (SPQ 5) ¹⁾	1 piece (SPQ 5) ¹⁾
Width	3 U Height					
HP	PCB depth 160 mm					
8	34812-108	34813-108			20808-062	20808-083
10	34812-110	34813-110			20808-004	20808-085
12	34812-112	34813-112			20808-064	20808-086
14	34812-114	34813-114	21101-853	21101-854	20808-065	20808-087
21	34812-121	34813-121			20808-066	20808-088
28	34812-128	34813-128			20808-067	20808-089
42	34812-142	34813-142			20808-068	20808-091
	PCB depth 220 mm					
8	34812-108	34813-108			20808-062	20808-083
10	34812-110	34813-110			20808-004	20808-085
12	34812-112	34813-112			20808-064	20808-086
14	34812-114	34813-114	21101-853	21101-854	20808-065	20808-087
21	34812-121	34813-121			20808-066	20808-088
28	34812-128	34813-128			20808-067	20808-089
42	34812-142	34813-142			20808-068	20808-091
Width	6 U Height					
HP	PCB depth 160 mm					
8	34812-608	34813-608			20808-062	20808-083
10	34812-610	34813-610			20808-004	20808-085
12	34812-612	34813-612			20808-064	20808-086
14	34812-614	34813-614	21101-855	21101-856	20808-065	20808-087
21	34812-621	34813-621			20808-066	20808-088
28	34812-628	34813-628			20808-067	20808-089
42	34812-642	34813-642			20808-068	20808-091
	PCB depth 220 mm					
8	34812-608	34813-608			20808-062	20808-083
10	34812-610	34813-610			20808-004	20808-085
12	34812-612	34813-612			20808-064	20808-086
14	34812-614	34813-614	21101-855	21101-856	20808-065	20808-087
21	34812-621	34813-621			20808-066	20808-088
28	34812-628	34813-628			20808-067	20808-089
42	34812-642	34813-642			20808-068	20808-091
Dimensions see page	7.82	7.82			7.82	7.82

1) SPQ (standard pack quantity): Part number includes 1 piece, but delivery is exclusively made in standard pack quantity (SPQ); please order at least the SPQ quantity or a multiple

Part no. includes one packing unit (PU); delivery is exclusively made in PU