




AMMDS 20-47/2 OPTO-COUPLER MODULE

IN: 35 VDC - OUT: 280 VAC / 2A

Triac 2 A
24 V DC
with minus plug link[Link to Product](#)**Illustration**



Product may differ from Image

Input

Voltage range ON	10...35 V DC
Voltage range OFF	0...3 V DC
Input current	6 mA
Plug link (supplied)	Art.-Nr. 90960
LED display	LED (red)

General data

Test isolation voltage	2.5 kV
Mounting method	DIN-rail mountable TH35 or G32 (EN 60715)
Housing	Black plastic, flame retardant
Temperature range	-20...+60 °C
Dimensions H × W × D	68×12×82 mm

Output

Switching voltage	24...280 V AC
Switching current per output	50 mA...2 A
Saturation voltage (across output)	max. 1 V AC
Leakage current (output is open)	max. 2 mA

Switching time ON/OFF	10/10 ms
Switching frequency	max. 20/5 Hz (resist./ind.)

Commercial data

country of origin	CZ
customs tariff number	85414090
minimum order quantity	1