


Data sheet Product LA 10 150 24





Cooling aggregates > Cooling aggregates with axial fan
160 x 83 mm, with axial fan

Features

width:	160 mm
height:	83 mm
length:	150 mm
thermal resistance:	0.2 - 0.055 K/W
surface:	<ul style="list-style-type: none"> raw degreased aluminium (by the metre raw aluminium) mounting area(s) milled flat
operating voltage of the fan motor:	<ul style="list-style-type: none"> 24 V DC 230 V AC

Technical Drawing



Fan

type:	ebmpapst 8314H
dimensions:	80x80x32 mm
tension:	24 V DC
power inout:	6 W
max. air volume:	80 m³/h
temperature range:	-20°C... 75°C
speed:	5,000 min⁻¹
noise level:	48 dB(A)
weight:	170 g
failure rate (L ₁₀):	L₁₀ > 55,000 h (40°C)

type:	ebmpapst 8556N
dimensions:	80x80x38 mm
tension:	230 V AC
power inout:	12 W
max. air volume:	50 m³/h
temperature range:	-40°C... +90°C
speed:	2,800 min⁻¹
noise level:	31 dB(A)
weight:	490 g
failure rate (L ₁₀):	L₁₀ > 52,500 h (40°C)

Fischer Elektronik GmbH & Co. KG
DEUTSCHLAND • GERMANY • ALLEMAGNE

Nottebohmstraße 28
58511 Lüdenscheid

Telefon +49 2351 435-0
Telefax +49 2351 45754

info@fischerelektronik.de
www.fischerelektronik.de