




SPECIFICATION CONTROL DRAWING Crystal Resonator

FREQUENCY

14.800000MHz



Holder Style	3X25X06 4-Pad
Mode	Fundamental
Adjustment Tolerance	± 10 PPM at 25°C
Temperature Stability	± 10 PPM
Operating Temp. Range	-20°C to +70°C
Load Capacitance	16 pF
ESR	150 Ohm
Drive Level	0.1 mW
Static Capacitance (C0)	7pF Max pF
Ageing	5PPM 1st Year Max
Marking	AEL148/WWYY

Amdt Date	Change Note	AEL Code
		X14M800000S001
		Issue Ref A