

## Conical countersink, 60°, HSSE, single-bladed cutter

for universal use up to 1300 N/mm<sup>2</sup>

**ORION**<sup>®</sup>

### Application:

For producing 60° counterbores up to 1300 N/mm<sup>2</sup>.

### Execution:

- profile-ground single-edge countersink

### Advantage:

- radial relief ensures optimum chip breaking
- deep and wide flute provides optimum chip removal



<b>Art. no.</b>	<b>11497 715</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	11497715
<b>Countersink angle</b>	60 Degree
<b>Cutting material</b>	HSSE
<b>Surface</b>	Uncoated
<b>Number of cutting edges</b>	1 PCS
<b>Tool holding device</b>	HA parallel shank
<b>Spot-facer diameter</b>	15 mm
<b>Min./max. cutting edge diameter</b>	2-15 mm
<b>Shank diameter</b>	10 mm
<b>Length</b>	65 mm
<b>f steel 1000</b>	0.14 mm/r
<b>Gross Weight</b>	0.100 kg
<b>Product Group</b>	1EH

### EAN

4053625031047