

## SWUC offset solid carbide boring bar, positive, left

For face turning and longitudinal turning using WC indexable insert

**ATORN**<sup>®</sup>



### Application

For face and longitudinal turning with WC indexable insert, 80°.

### Execution

- Precision-manufactured boring bar, **steel**, with internal cooling, offset, type C, attack angle 93°, tip angle 80°, clearance angle 7°

### Advantage

- Universal use for face and longitudinal turning
- Positive geometry for the body ensures low cutting forces

<b>Art. No.</b>	<b>17827 250</b>
<b>ISO name</b>	E 0508H SWUC R/L 02
<b>Min. bore diameter</b>	5.8 mm
<b>Tapered diameter</b>	5 mm
<b>Shaft diameter</b>	8 mm
<b>Clearance length</b>	18 mm
<b>Length</b>	100 mm
<b>Clamping surface height</b>	7 mm
<b>Programming size</b>	2.9 mm
<b>Suitable for indexable inserts</b>	WC.. 0201..
<b>Tool design</b>	Left
<b>DIN</b>	8024

### EAN-Code

405029339039 1