

## Micrometer

Baked enamel-finished frame

Mitutoyo

### Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

### Execution:


- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces
- Friction coupling for consistent, repeatable measuring force

### Advantage:

- Baked enamel-finished frame

### Delivery:

Including box, setting standard (from 25 mm), adjustment wrench, up to 50 mm with factory test certificate



<b>Art. no.</b>	<b>32016 070</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	103-164
<b>Min./max. length measuring range</b>	675-700 mm
<b>Vernier scale</b>	0.01 mm
<b>Measuring surface diameter</b>	8 mm
<b>Measuring spindle increments</b>	0.5 mm
<b>Bracket depth</b>	382 mm
<b>Spindle clamping</b>	Yes
<b>Error limit</b>	9 µm
<b>Display</b>	Nonius
<b>Min./max. measurement force</b>	5-15 N
<b>Calibration Group</b>	D
<b>Gross Weight</b>	10.000 kg
<b>Product Group</b>	3MA

### EAN

4946368004303