

cabinet workbench series V 2000 with knee space

Universal coating 2000 mm, 5 drawers with full extension



Application:

for seated working

Execution:

- Solidly welded steel sheet construction
- Base made of square-section steel tube 45 x 45 x 2 mm, with level compensation
- 2 drawers with 100% full extension on the left, 1 x front height 180 mm, 1 x front height 360 mm, recessed shelf in the centre, 3 drawers, front height 180 mm on the right



Art. no.	50201 718
Number of drawers	5 PCS
Working height	850 mm
Number of doors	1 PCS
Worktop width	2000 mm
Pullout type	Full extension
Worktop height	50 mm
Colour of front	Optional
Worktop depth	700 mm
Cabinet colour	Optional
Drawer surface	0.27 m ²
With single pull-out safety brake	Yes
Levelling	Yes
Lock type	DOM® locking system
Drawer front height	4 x 180 mm, 1 x 360 mm
Drawer width (inner dimension)	500 mm
Surface	Powder-coated
Drawer width (inner dimension) x drawer depth (inner dimension)	500 x 540 mm
Load-carrying capacity	1500 kg
Drawer depth (inner dimension)	540 mm
Load-carrying capacity per drawer	100 kg
Material of worktop	Universal covering
Central locking	Yes
Product Group	Prod. Gr. 502

EAN

4014641011017