

Pneumatic impact wrench RRI-2500M



Execution:

- Motor housing made of composite
- Air outlet through handle
- Rotating air connection
- Adjustable power, two positions
- Left/right switch on the trigger for single-handed operation
- Two-stage trigger for controlled screwing-in

Advantage:

- Compact and lightweight
- Mechoneer impact mechanism



Art. no.	75066 236
Brand	RED ROOSTER
Manufacturer Part Number	RRI-2500M
Model	RRI-2500M
Suitable for screw	M24
Max. tightening torque	2000 Nm
Max. releasing torque	2700 Nm
Max. idle speed	5500 rpm
Air consumption	16 l/s
Tool holding device	3/4-inch external square
Hammer mechanism system	Twin hammer mechanism
Length	187 mm
Housing width	45 mm
Inner hose diameter	13 mm
Sound-pressure level	96 dB
Weight	3.58 kg
With right/left-hand rotation	Yes
Gross Weight	3.580 kg
Product Group	7AE

EAN

8717981400805