



MSD Platinum (Touring/Stage)

MSD Platinum 25 R 1CT/8

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data



General Information		Operating and Electrical	
Operating Position	UNIVERSAL [Any or Universal (U)]	Power Consumption	550 W
Life to 50% Failures (Nom)	1,500 hour(s)		
Light Technical		Controls and Dimming	
Color Code	2	Dimmable	Yes
Luminous Flux	26,000 lm		
Chromaticity Coordinate X (Nom)	297	Mechanical and Housing	
Chromaticity Coordinate Y (Nom)	303	Net Weight (Piece)	108.000 g
Correlated Color Temperature (Nom)	8000 K		
Arc Length O (Nom)	1.4 mm	Product Data	
		Order product name	MSD Platinum 25 R 1CT/8
		Full product name	MSD Platinum 25 R 1CT/8
		Full product code	871869961403400

MSD Platinum (Touring/Stage)

Order code	928495905314
Material Nr. (12NC)	928495905314
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699614034


Numerator - Packs per outer box	8
EAN/UPC - Case	8718699614041

Dimensional drawing



Product	D (max)	O	C (max)
MSD Platinum 25 R 1CT/8	54.5 mm	1.4 mm	60 mm

Photometric data



Spectral Power Distribution Colour - MSD Platinum 25 R 1CT/8

