



RMMDA 11/230 OUTPUT RELAY

IN: 230 VAC/DC - OUT: 250 VAC/DC / 6 A

1 relay; 1 NO contact
6 A
230 V AC
with minus plug link

[Link to Product](#)**Illustration**



Product may differ from Image

Utilization category

AC-15	4 A (24/110/230 V AC)
AC-1	6 A (24/110/230 V AC)
DC-13	2 A (24 V DC); 0.25 A (110 V DC); 0.1 A (230 V DC)

Input

Connection voltage - current	230 V AC/DC (195...253 V AC/DC) - 4.5 mA without plug link
LED display	LED (red)

General data

Mech./ elect. life	20.000.000 switching cycles/load dependent
Mounting method	DIN-rail mountable TH35 or G32 (EN 60715)
Temperature range	-20...+50 °C
Test isolation voltage	4 kV
Dimensions H × W × D	82×12×68 mm

Output

Switching voltage	max. 250 V AC/DC
Switching current per output	max. 6 A
Min. load current	100 mA
Power rating (voltage dependent)	max. 2000 VA/240 W
Switching frequency	max. 10 Hz
Contact material	Ag Ni
Energize/release/contact bounce time	10/15/2 ms

Commercial data

country of origin	CZ
customs tariff number	85364900
minimum order quantity	1