


Plug type compact connector ready-made with cable

ST 18/3pole




rated voltage: 250 V~
 permanent temperature: 110°C male/female part, 70°C cable
 protection: IP 20 as per DIN 40050
 materials: insulating parts: thermoplastics, contact parts: brass plated with surface treatment
 cables: H 05 VV - F 3 G 1,5/2,5
 approvals:




storage types ref. no.

lengths	1.5 mm ² black	1.5 mm ² white
0.5 m	94.732.0500.1	94.732.0500.2
1.0 m	94.732.1000.1	94.732.1000.2
1.5 m	94.732.1500.1	94.732.1500.2
2.0 m	94.732.2000.1	94.732.2000.2
2.5 m	94.732.2500.1	94.732.2500.2
3.0 m	94.732.3000.1	94.732.3000.2
3.5 m	94.732.3500.1	94.732.3500.2
4.0 m	94.732.4000.1	94.732.4000.2




cable end 35 mm
 insulating length 7 mm




0.5 m	94.732.0503.1	94.732.0503.2
1.0 m	94.732.1003.1	94.732.1003.2
1.5 m	94.732.1503.1	94.732.1503.2
2.0 m	94.732.2003.1	94.732.2003.2
2.5 m	94.732.2503.1	94.732.2503.2
3.0 m	94.732.3003.1	94.732.3003.2
3.5 m	94.732.3503.1	94.732.3503.2
4.0 m	94.732.4003.1	94.732.4003.2

cable end 35 mm
 insulating length 7 mm



0.5 m	94.732.0504.1	94.732.0504.2
1.0 m	94.732.1004.1	94.732.1004.2
1.5 m	94.732.1504.1	94.732.1504.2
2.0 m	94.732.2004.1	94.732.2004.2
2.5 m	94.732.2504.1	94.732.2504.2
3.0 m	94.732.3004.1	94.732.3004.2
3.5 m	94.732.3504.1	94.732.3504.2
4.0 m	94.732.4004.1	94.732.4004.2



1.5 m	94.732.1507.1	94.732.1507.2
2.0 m	94.732.2007.1	94.732.2007.2
2.5 m	94.732.2507.1	94.732.2507.2

¹⁾ Available only with screw-mounted 2-pole angled plug with 2 protective ground contact systems as per DIN 49441 Form R2/CEE 7 Standard sheet VII


750-438-7505

250 V~, 16 A

diameters

6/26

ST 18/3



Cable lengths

We deliver the ready-made plug connector ST 18/3 with cable lengths from 0.5 m to 4 m (in steps of 0.5 m) pre-mounted.

The tolerance in cable lengths is $\pm 3\%$. Intermediate and over-lengths are available upon request.

Minimum order per cable length: 50 pcs

The cables are available with cross-sections of 1.5 mm².

Male/female parts with similar coding are available in black and in white.

