

Thermal Mini Printer
AP1300 and AP1310 Series



H=47, W=92, D=108mm



H=65, W=95, D=128mm

- Compact, portable and stylish
- Single handed paper load operation
- High speed and high quality fixed head thermal mechanism
- Choice of serial RS232, IrDA or Bluetooth interface
- Applications include mobile ticketing and recording, PDA printing, utility billing, in-vehicle receipting, test and measurement equipment and medical systems
- AP1300 has 16m roll capacity and AP1310 has 38m roll capacity
- Choice of rechargeable or primary cell battery power (Note: The AP1310-DP is a mains powered only version with UK, Euro and USA mains plugs and no batteries)
- Linerless, label sticky paper roll is available
- An optional fast charger is available which has both mains and 12V in-car inputs

Contents: Printer, rechargeable battery pack, cradle for AA batteries, UK/US/euro mains trickle charger, 2 paper rolls, D9 data cable, wall mount bracket, belt clip and user guide

Specification:	AP1300/AP1310	AP1300-IR/AP1310-IR	AP1300-BT/AP1310-BT
Order Code	109-5829/109-5832	109-5830/109-5834	109-5831/109-5835
Data input	RS-232	RS-232	RS-232
Wireless data input	N/A	IrDA	Bluetooth
Printer type	Fixed head thermal mechanism (Fujitsu FTP-628MCL103)		
Print speed	60 mm/s (at 7.2V battery voltage); 50 mm/s (typical)		
Print Width	48 mm		
Dots per line	384		
Dot spacing	8 dots/mm (vertical and horizontal)		
Weight	AP1300 series: 330g (including battery and paper roll) AP1310 series: 446g (including battery and paper roll)		

419105

Mftrs. List No.	Order Code	Price Each
AP1300	109-5829 ●	
AP1300-IR	109-5830 ●	
AP1300-BT	109-5831 ●	
AP1310	109-5832 ●	
AP1310-IR	109-5834 ●	
AP1310-BT	109-5835 ●	
AP1310-DP	109-5836 ●	
Paper Roll, AP1300, 15m	109-5837	
Paper Roll, AP1310, 33m	109-5838	
Linerless Roll, 18x8.5m, AP1300	135-0610	
Linerless Roll, 8x28m, AP1310	135-0611	
Fast Charger (Mains/in-car)	109-5839 ●	