



DELL TB16 Kabelgebunden Thunderbolt 3 Schwarz

Marke : DELL

Artikel-Code: 5K5RK

Produktname : TB16

DELL TB16. Übertragungstechnik: Kabelgebunden, Hostschnittstelle: Thunderbolt 3, HDMI-Version: 1.4a. Ethernet LAN Datentransferraten: 10,100,1000 Mbit/s. Produktfarbe: Schwarz, Slot-Typ Kabelsperre: Kensington, Markenkompatibilität: Dell. Energiequelle: AC, Stromversorgung: 180 W. Unterstützt Windows-Betriebssysteme: Windows 10, Windows 7, Windows 8, Windows 8.1, Unterstützte Linux-Betriebssysteme: Ubuntu 14.04



Anschlüsse und Schnittstellen		Leistungen	
Übertragungstechnik *	Kabelgebunden	Kabelsperre-Slot	✓
Hostschnittstelle *	Thunderbolt 3	Slot-Typ Kabelsperre	Kensington
Anzahl USB 2.0 Anschlüsse *	2	Produktfarbe *	Schwarz
USB 3.2 Gen 1 (3.1 Gen 1) Anzahl der Anschlüsse vom Typ A *	3	LED-Anzeigen	✓
Anzahl HDMI-Anschlüsse *	1	Markenkompatibilität	Dell
HDMI-Version	1.4a	Energie	
Anzahl VGA (D-Sub) Anschlüsse	1	Energiequelle	AC
Anzahl DisplayPort Anschlüsse	1	Stromversorgung	180 W
Anzahl Mini DisplayPorts	1	Software	
Anzahl Thunderbolt 3 Anschlüsse	1	Unterstützt Windows-Betriebssysteme	Windows 10, Windows 7, Windows 8, Windows 8.1
Mikrofon-Eingang *	✗	Unterstützte Linux-Betriebssysteme	Ubuntu 14.04
Kombinierter Kopfhörer-/Mikrofon-Anschluss	✓	Betriebsbedingungen	
Kopfhörer-Anschluss	3,5 mm	Betriebstemperatur	0 - 35 °C
Line-out	✓	Temperaturbereich bei Lagerung	-20 - 60 °C
USB-Stecker	USB Typ-A, USB Typ-C	Relative Luftfeuchtigkeit in Betrieb	10 - 80%
Gleichstrom-Anschluss (DC)	✓	Luftfeuchtigkeit bei Lagerung	5 - 90%
Netzwerk		Gewicht und Abmessungen	
Ethernet/LAN *	✓	Breite	145 mm
Anzahl Ethernet-LAN-Anschlüsse (RJ-45)	1	Tiefe	145 mm
Ethernet LAN Datentransferraten	10,100,1000 Mbit/s	Höhe	52 mm
Leistungen		Gewicht	720 g
Integrierter Kartenleser *	✗	Lieferumfang	
		Mitgelieferte Kabel	Thunderbolt
		AC-Netzadapter	✓
		Betriebsanleitung	✓



0884116256809



884116256809

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 15-MAR-2024. Prints or copies of Information are only valid on the printed Publication date