

ToLEDo Vintage G200 DIMMABLE

ToLEDo Vintage G200 GL DIM 300LM 820 E27 SL
0029920



Product features

- New and innovative Flexible Filament Chip Technology (FFCT) designed to create the low-lit vintage effect
- Low glare - suitable for low height installation
- 2000K colour temperature, to create a cosy ambience
- Golden tinted glass envelope
- 15,000 hours average rated life - last 7.5 times longer than incandescent vintage lamps
- Unique filament construction design - 'Spiral' shape
- Omni-directional light distribution - 300°
- Low-lumen output to create low-lit effect - 300lm
- More than 100,000X switching cycles
- 3 years warranty
- Environment friendly - no mercury and lower CO2 emissions
- Dimmable on approved dimmers
- Ideal for hotels, restaurants, heritage lighting, bars and decorative applications



PRODUCT OVERVIEW

Product name	ToLEDo Vintage G200 GL DIM 300LM 820 E27 SL
Technology	LED
Watt (Rated) (W)	5.5
Type	LED exchangeable
Cap/Base	E27
Fixture rating	Open
General application	Residential & Consumer
ETIM Class	EC001959
E-number FI	4740757
Warranty	3 years
Luminous flux (lm)	300
Colour temperature (K)	2000
Light colour	Candlelight
CRI (Ra)	80
Colour Consistency (SDCM)	6
Beam Angle (°)	300
Wattage (W)	5.5
Product Voltage (V)	230
Dimmable	Yes
Average life (Nominal) (h)	15000
IP rating	IP20
Product EAN number	5410288299204

DATA TABLE

General data

Product name	ToLEDo Vintage G200 GL DIM 300LM 820 E27 SL
Technology	LED

ToLEDo Vintage G200 DIMMABLE

ToLEDo Vintage G200 GL DIM 300LM 820 E27 SL

0029920

Watt (Rated) (W)	5.5
Type	LED exchangeable
Cap/Base	E27
Fixture rating	Open
General application	Residential & Consumer
Operating temperature range (°C)	-10°C...+45°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001959
E-number FI	4740757
Warranty	3 years

Optical data

Luminous flux (lm)	300
Luminous flux (Rated) (lm)	300
Colour temperature (K)	2000
Light colour	Candlelight
CRI (Ra)	80
Colour Consistency (SDCM)	6
Beam Angle (°)	300
Lumen maintenance at end of nominal life (%)	70

Electrical data

Wattage (W)	5.5
Equivalent watt (W)	28
Starting time (max) (s)	0.5
Warm-up time to 60% of full light (max) (s)	1
Product Voltage (V)	230
Lamp power factor	0.9
No. Of switching cycles before premature failures	>100000
Transformer required	No
Dimmable	Yes
Nominal Frequency (Hz)	50/60Hz

Lifetime data

Average life (Nominal) (h)	15000
Average life (Rated) (h)	15000

Physical data

IP rating	IP20
Nominal Product Length (mm)	283
Nominal Product Diameter (mm)	200
Weight (kg)	0.3

Packaging

Single packaging type	Carton
Product EAN number	5410288299204

ToLEDo Vintage G200 DIMMABLE

ToLEDo Vintage G200 GL DIM 300LM 820 E27 SL

0029920

Packaging single length / height (cm)	31.8
Packaging single width (cm)	22.3
Packaging single depth (cm)	22.3
DUN14 (outer)	15410288299201
Units per outer package	2
Packaging outer length / height (cm)	49.7
Packaging outer width (cm)	27.2
Packaging outer depth (cm)	34.0

Safety data

Optimal operating condition (°C)	-10-45
Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Safety message	Not Suitable for totally enclosed fixtures
Safety message	Dimmable with approved dimmers