

Precision pointer micrometer

MAHR 40 T/1003



Application:

For quick testing of parts from series production.

Version:

- Adjustable tolerance marks
- Carbide measuring faces
- Strong steel bracket
- Movable measuring probe for lifting the anvil

Delivery:

In case, precision pointer included



Art. no.	31472 105
Min./max. length measuring range	0-25 mm
Indicating calliper measuring range	+/- 0.05 mm
Digit increment, micrometer	0.01 mm
Digit increment, indicating calliper	0.001 mm
Micrometer error limit	0.002 mm
Indicating calliper error limit	0.001 mm
Measuring spindle increments	0.5 mm
Spindle clamping	Yes
Measurement force	6.5 N
Measuring surface diameter	7.5 mm
Calibration Group	AN
DIN	863

EAN-Code

4059 192004675