

## Pneumatic belt sander GB 14000

MANNESMANN  
DEMAG

### Application:

For sanding on free belt or with belt support contact

### Version:

- With sanding belt cooling
- With replaceable contact arms
- For 6-mm and 13-mm belt widths
- Exhaust: front

### Delivery:

Sanding arm 610x13mm, hose unit



<b>Art. no.</b>	<b>75061 160</b>
<b>Model</b>	GB 1400
<b>Valve design</b>	Lever valve
<b>Max. belt speed</b>	20 m/s
<b>Max. idle speed</b>	20000 rpm
<b>Power input</b>	400 W
<b>Air consumption</b>	14.1 l/s
<b>Connection thread</b>	IT 1/4 inch
<b>Length</b>	371 mm
<b>Min. sanding belt width</b>	6 mm
<b>Max. sanding belt width</b>	13 mm
<b>Weight</b>	1.4 kg
<b>Grinding belt length</b>	610

### EAN-Code

4251757302800