

Between Series Adaptor 33_BNC-BK-50-1/133_U

Description

Adaptor plug/jack
BNC plug (male) / BK jack (female)

Interface standards
Series BNC - IEC 61169-8_MIL-STD-348A/301_CECC 22120
Series BK - SUHNER-BK



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 4 GHz

Mechanical Data

Number of matings 500
Weight 0.0118 kg

Environmental Data

Operating temperature °C to °C
2011/65/EU (RoHS - including compliant
2015/863 and 2017/2102)

Material Data

Interface - BNC plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Interface - BK jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	

Related Documents

Outline drawing DOU-00014405

Ordering Information

Single package 33_BNC-BK-50-1/133_UE