



Photo lamps

Set lights for B/W and colour photography and video


For special features, specific benefits and areas of use see page 143



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter D max. mm	Total length L max. mm	Light centre length LCL mm	Lumi- nous flux lm	Average life h	Colour temperature K	Burning position	PU
77841413	240V 500W B22d A.80x159.5	240	530		B22d	81	163.5		14,400	6	3,400	any	
77841414	220V 500W E27 A.80x166	220	530		E27	81	165		14,400	6	3,400	any	
77841408	240V 500W E27 A.80x166	240	500		E27	81	165		14,400	6	3,400	any	



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter D max. mm	Total length L max. mm	Light centre length LCL mm	Lumi- nous flux lm	Average life h	Colour temperature K	Burning position	PU
00845275	230V 250W E27/27 60x105 blue	230	250		E27	61	105		3,400	25	ca. 4,000		



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter D max. mm	Total length L max. mm	Light centre length LCL mm	Lumi- nous flux lm	Average life h	Colour temperature K	Burning position	PU
77841403	240-250V 275W B22d A.60x102.5	240-250	275		B22d	61	105.5		7,400	4	3,400	any	