



LED Panels

Description

LED backlit panel solution for a range of commercial applications

Features

- TP(b) rated panel, suitable for a number of commercial suspended ceiling applications
- Available for suspended ceilings with 600x600mm and 1200x600mm systems
- Cool White 4000K and Daylight 6000K versions available
- Back lit design for increased lumen efficiency
- External (ENEC Approved) driver, with loop-in loop-out capability
- Plug in emergency pack option (BR1191)
- Surface and suspension mounting accessories available
- UGR<21 in compliance with BS EN12464-4
- 5-year guarantee for panels

Technical Specification

Voltage	220V-240V	
Frequency	50-60Hz	
Power Factor	≤0.9	
Colour Temperature	4000K and 600K option	
Construction	Polycarbonate	
IP Rating	IP20	
IK rating	IK02	
Dimmable	No	
Light Source	Non-replaceable LED	
Lifespan	50,000hrs	
	100W	12,000lm
	150W	19,500Lm
Luminous Flux	32W	3500 Lm
	45W	5500 Lm
Luminous Efficacy	32W	110 Lm/W
	45W	120 Lm/W
Standards	BS EN 60598-1	

Range

225-7019	32W LED Panel 4000K
225-7020	32W LED Panel 6000K
225-7021	45W LED Panel 4000K
225-7022	45W LED Panel 6000K
202-7263	Remote 3 Hour Emergency Pack
202-7264	Surface Mounting Kit for 600x600 Panel
202-7267	Surface Mounting Kit for 1200x600 Panel
202-7266	Wire Suspension Kit

Dimensions

	Length	Width	Depth
225-7019	595mm	595mm	34mm
225-7020	595mm	595mm	34mm
225-7021	1195mm	595mm	32mm
225-7022	1195mm	595mm	32mm
202-7264	601mm	601mm	70mm
202-7267	1201mm	601mm	70mm

No Serviceable parts

Contact your local authority for information concerning the correct disposal of your product