


# 30818-331 FRONT PANEL, UNSHIELDED, 3 U, 63 HP, 2.5 MM, AL, ANODIZED, UNTREATED EDGES





# **KEY FEATURES**

Partial width front panel, Al, 2.5 mm

Al, clear anodized, untreated edges

# **PRODUCT ATTRIBUTES**

Accessory Type: Front panel

Type: Front Panel without Handle

Handle Type: None

Mounting: Screw-on Front

EMC Shielding: No

Material: Aluminum

Front Finish: Anodized

Rear Finish: Anodized

Treated Edges: No

Rack Height: 3 U

Height: 128.4 mm

Rack Width: 63 HP

Width: 319.7 mm

Depth: 2.5 mm

Complies With: IEC 60297-3-101; IEEE 1101.1/10

Package Quantity: 1

## ADDITIONAL PRODUCT DETAILS

Front Panel, anodized with untreated edges, unshielded. The panels enable mounting on horizontal rails.

Please order fixing material (sleeves, collar screws) separately.

#### **CERTIFICATIONS**



## North America

All locations +1.763.422.2661 Chat with us: schroff.nyent.com

#### Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: schroff.nvent.com

#### Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: schroff.nvent.com

## Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: schroff.nvent.com



Our powerful portfolio of brands:

© 2023 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

nVent.com CADDY ERICO