



Part no.: 50122337
K-Y1 M12A-20m-M12A-S-PUR
Interconnection cable

Figure can vary

Contents

- Technical data
- Electrical connection

Part no.: 50122337 – K-Y1 M12A-20m-M12A-S-PUR – Interconnection cable

Technical data

Basic data

Suitable for CML700i light curtains

Connection

Connection 1

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	5 -pin
Encoding	A-coded
Design	Axial

Connection 2

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	5 -pin
Encoding	A-coded
Design	Axial

Connection 3

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	8 -pin
Encoding	A-coded
Design	Axial

Cable properties

Shielded	Yes
Cable length fork 1	20,000 mm
Cable length fork 2	150 mm
Sheathing material	PUR

Classification

Customs tariff number	85444290
eCl@ss 8.0	27279218
eCl@ss 9.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855

Electrical connection

Connection 1	
Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	5 -pin
Encoding	A-coded

Part no.: 50122337 – K-Y1 M12A-20m-M12A-S-PUR – Interconnection cable

Connection 1	
Design	Axial

Connection 2	
Type of connection	Connector
Thread size	M12
Type	Male
Handle body material	
No. of pins	5 -pin
Encoding	A-coded
Design	Axial
Lock	

Connection 3	
Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	8 -pin
Encoding	A-coded
Design	Axial