



AMMDS 10-44/0,1 OPTO-COUPLER MODULE

IN: 53 VDC - OUT: 40 VDC / 0,1 A

Transistor 0.1 A
24 V DC
with minus plug link
Double terminals on the output side

[Link to Product](#)**Illustration**



Product may differ from Image

Input

LED display	LED (red)
Input current	6 mA
Plug link (supplied)	Art.-Nr. 90960
Voltage range ON	10...53 V DC
Voltage range OFF	0...3 V DC

General data

Mounting method	DIN-rail mountable TH35 or G32 (EN 60715)
Housing	Black plastic, flame retardant
Temperature range	-20...+60 °C
Test isolation voltage	3.75 kV
Dimensions H x W x D	82x12x64 mm

Output

Switching voltage	4...40 V DC
Switching current per output	1 mA...0.1 A
Saturation voltage (across output)	max. 1.2 V DC
Leakage current (output is open)	max. 0.3 mA
Switching time ON/OFF	1.5/2 ms
Switching frequency	max. 300/40 Hz (resist./ind.)

Commercial data

country of origin	CZ
customs tariff number	85414090
minimum order quantity	1