


M12 MALE ON REAR OF MSUD VALVE PLUG FORM BI 11MM


Form BI (11 mm) – M12, connector at the rear
without components
3-pole

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration



stay connected

Product may differ from Image

Approvals



Form

42041

Technical Data

Operating voltage	125 V AC/DC
Operating current per contact	max. 4 A
Configuration	2 contacts + PE
Protection	IP67 inserted and tightened (EN 60529)
Locking of ports	M3/M12 × 1 mm (recommended torque 0.4/0.6 Nm)

General data

Temperature range	-25...+85 °C
-------------------	--------------

Commercial data

country of origin	CZ
customs tariff number	85369010
minimum order quantity	1