

Product type designation

Product description

RUGGEDCOM 2488-24FG54 Module CC

4 x 1000LX SFP - Singlemode, 1310 nm, LC, 70 km Module with Conformal Coating
RUGGEDCOM 2488-24FG54 MODULE CC 4 X 1000LC - SINGLEMODE 1550NM, SFP, 70KM WITH CONFORMAL COATING



Suitability for operation

RSG2488

Interfaces

Number of electrical/optical connections / for network components or terminal equipment / maximum

4

Number of optical interfaces / for network components or terminal equipment / maximum

4

Design of the optical interface / for network components or terminal equipment

LC

Range / at the optical interface / depending on the optical fiber used

70 km

Permitted ambient conditions

Ambient temperature

- during operation
- during storage
- during transport
- Note

-40 ... +85 °C

-40 ... +85 °C

-40 ... +85 °C

A maximum ambient operating temperature of +85 °C is permissible for a duration of 16 hours

Relative humidity / at 25 °C / without condensation / during operation / maximum

95 %

Protection class IP

IP20

Design, dimensions and weight

Design

Media module

Width

110 mm

Height	22 mm
Depth	91 mm
Net weight	0.43 kg
Coating	Conformal Coating
Mounting type	screwed
<ul style="list-style-type: none"> • Installation in media module slot 	Yes

Standards, specifications, approvals

Standard	<ul style="list-style-type: none"> • for EMC • for safety / from CSA and UL • for hazardous zone / from CSA and UL • for emitted interference • for interference immunity 	<p>FCC Part 15 (Class A), EN55022 (CISPR22 Class A)</p> <p>UL 60950-1, CSA C22.2 No. 60950-7</p> <p>Hazardous Locations: Class 1 Division 2</p> <p>EN 61000-6-4 (Class A)</p> <p>EN 61000-6-2</p>
Certificate of suitability	<ul style="list-style-type: none"> • CE marking • C-Tick • KC approval • E1 approval • IEC 61850-3 	<p>EN 61000-6-2, EN 61000-6-10</p> <p>Yes</p> <p>No</p> <p>No</p> <p>No</p> <p>Yes</p>

Further Information / Internet Links

Internet-Link	<ul style="list-style-type: none"> • to website: Industry Mall/RUGGEDCOM selector • to website: Siemens RUGGEDCOM • to website: Selector for cables and connectors • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAx Download Manager • to website: Industry Online Support 	<p>http://ruggedcom-selector.automation.siemens.com</p> <p>http://siemens.com/ruggedcom</p> <p>http://www.siemens.com/snst</p> <p>http://www.siemens.com/simatic-net</p> <p>https://mall.industry.siemens.com</p> <p>http://www.siemens.com/automation/net/catalog</p> <p>http://automation.siemens.com/bilddb</p> <p>http://www.siemens.com/cax</p> <p>https://support.industry.siemens.com</p>
---------------	--	--

last modified:

16.03.2015