

Industrial Pt100 probe with Terminal Head,Extension& replaceable insert

Heavy duty Pt100 probe with an aluminium terminal head,lagging extension and optional,replaceable insert.

Specifications

Sensor Type	Pt100, class B, 4 wire to IEC 60751
Probe material	316 stainless steel, welded tip,6mm x 150mm
Extension	12.5mm diameter x 75mm
Process connection	1/2 inchBSP,stainless steel thread
Optional insert	Replaceable,spring loaded insert
Tip temperature Rating	-50°C to +450°C
Terminal Head	Aluminium with captive, threaded cover housing a DIN terminal block
Assembly rating	IP67
Cable entry	M20 cable gland

Probe dia(mm)	Probe length (mm)	Farnell code	Lab code
6	150	7088449	010008TD



Data Ref: FAR 30A

