

Compaq W220q 22" Widescreen Flat Panel Monitor

Compaq W220q 22-inch Wide flat-panel monitor provides superb picture quality at a great cost



Specifications

- Display Size 22" (55.9 cm) wide diagonal (H= 29.6 cm , W= 47.4 cm)
- Faceplate treatment Antiglare polarizer, Antistatic
- Pixel pitch 0.282 mm
- Refresh response time 5ms on/off (Typical)
- Brightness 300 cd/m2 (typical)
- Contrast ratio 1000:1(typical)

Interface specifications

- Analog (15-pin mini D-sub VGA) - cable included
- Display resolution 1680 x 1050 @ 60Hz max
- Recommended resolution 1680 x 1050 @ 60Hz (native recommended)
- True colour (up to 16.7M)
- Horizontal scan rates 56 to 76Hz vertical, 30 to 81Hz horizontal

Features

- Two integrated stereo speakers (2w per channel) with front volume control
- Viewing angle 170° horizontal, 160° vertical
- Plug and play Yes

Power

- Power Consumption 55 watts maximum in operating mode; 2 watts max in power saving mode

Mechanical specifications

- Weight 6.6Kg
- Package Dimensions (W x D x H) 625 mm x 210 mm x 530 mm
- Package Weight 10.0Kg
- Operating Temperature Range 5°C to 35°C, 20-85% non-condensing Relative Humidity
- Storage Temperature Range -20°C to 60°C, 5-95% non-condensing Relative Humidity

Regulatory

- Compliance Industry Standards CB, CE, TuV, FCC Class B, ICES, S-Mark, VCCI, CCC, BSMI, KETI, C-Tick, CECP

Additional information

- Warranty Limited one-year parts and repair labour warranty (may vary depending on the country)
- Box Content Monitor, VGA cable (1.8m) , AC power cord (1.9m), Stereo audio cable (1.5m), Limited Warranty card
- KK978AA#ABB (Europe), UPC 883585858750
- KK978AA#ABU (UK & Ireland), UPC 883585858767
- KK978AA#AR8 (Switzerland), UPC 883585858774
- KK978AA#ABY (Denmark), UPC 883585858781
- KK978AA#B14 (Belgium), UPC
- KK978AA#ABV (Middle-East), UPC

COMPAQ