


Item code

CDSHM 27



Brief description:

male insert, 27 poles, Spring connection contacts SQUICH, 10A, 400V, silver plated, size "77.27", CLASS inserts

Product description	
Model	male insert
Version	Spring connection contacts SQUICH
Series	CDSH
Product type	with male contacts
Family	CLASS inserts
Size	size "77.27"
N° of poles	27 poles + 
Technical data	
Current	10 A (A.C. and D.C.)
Voltage	400 V
Sustained impulse voltage	6kV
Pollution degree	3
Wire section	0,14 mm ² - 2,50 mm ²
AWG size	26 - 14
Operating temperature range (min, max)	-40°C ... +125°C
Contact type	silver plated
Plugging cycles	≥ 500
IP degree of protection	IP20 without enclosure; IP65/IP66/IP67/IP68 with enclosure
Wire cross section PE	0,14 - 4 mm ² ; AWG 20 - 12
Other technical details	
Insulation resistance	≥ 10 GΩ
Weight	46,00 g

Approvals / Standards	
Reference standard	EN 61984 (2001-11)
General ordering information	
EAN code	8015747222624
Tariff number	85369095
Packaging Information	
Packaging length	245,00 mm
Packaging height	165,00 mm
Packaging width	215,00 mm
Packaging weight	1,38 kg
Packaging volume	8,69 dm ³
Packaging description	Carton box
Packaging quantity	30 Pcs
Packaging EAN code	8015747222792
Sub-packaging length	197,00 mm
Sub-packaging height	55,00 mm
Sub-packaging width	113,00 mm
Sub-packaging weight	0,23 kg
Sub-packaging volume	1,22 dm ³
Sub-packaging description	Carton
Sub-packaging quantity	5 Pcs
Sub-packaging EAN barcode	8015747222808



Item code

CDSHM 27



Notes

actuator button connections



Reopening